


NX CAM Tips

2. 優化進給率

使用優化進給率選項可以更高效，更平穩的除料，同時延長刀具壽命。此選項會監測刀具的切削狀態，通過對進給率的調整，以維持刀具以更加平穩的材料去除率來工作。

此功能使用 3D IPW 模型或毛坯幾何體計算進給率。

如下圖的例子：



你可以在 Operation navigator 裡使用它，方法是選擇需要優化的 operation，選擇滑鼠右鍵 → Tool Path → Optimize Feed Rate.

或者你可以在銑加工編輯對話方塊裡選擇 → Feeds and Speeds  → Feed Rates group → Optimize Feed Rate When Generating。

Teamcenter Tips

3. 如何重新生成 TCAWorkSpace-TileCollection ?

問題：


TCAWorkSpace-TileCollection 被意外刪除，如何重新生成？

方法：


如果僅僅是 Tile Collection (TCAWorkSpace) 被刪除，你可以通過下面的命令去重新生成：

```
aws2_install_tilecollections -u=infodba -p=*** -g=dba -mode=add -  
file=%TC_INSTALL_DIR%/aws2/data/Awp0aws2GatewayTileCots_Install.xml -  
log=c:\temp\tilelog.txt
```

日誌檔顯示命令成功執行：



```
1 Info: Total number of Tile Template(s) definitions in XML is 13  
2 Total number of Tile Template(s) already in Db 13  
3 Total number of Tile Template(s) created 0  
4  
5 Info: Total number of Tile(s) definitions in XML is 11  
6 Total number of Tile(s) already in Db 11  
7 Total number of Tile(s) created 0  
8  
9 Info: Tiles added to TCAWorkspace-TileCollectionInbox, Folders, Saved Searches, Help, Favorites, My  
10 Info:  
11
```



Greater China
ME&S Service Team
PRC Helpdesk (Mandarin): 800-810-1970/021-22086635
Taiwan Helpdesk (Mandarin): 00801-86-1970
HK Helpdesk (Cantonese): 852-2230-3322
Global Technical Access Center: <http://www.siemens.com/gtac>
Siemens PLM Software Web Site: <http://www.plm.automation.siemens.com>
Siemens PLM Software (China) Web Site: http://www.plm.automation.siemens.com/zh_cn/

此e-mail newsletter 僅提供給享有產品支援與維護的Siemens PLM 軟體使用者。當您發現問題或希望棄訂，請發送郵件至 helpdesk_cn.plm@siemens.com 聯繫，如棄訂，請在標題列中注明“棄訂”